

Adaptive gripper fingers DHAS

FESTO



Adaptive gripper fingers DHAS

Features

FESTO

At a glance

Adaptive gripper fingers for smooth and flexible gripping, with the Fin Ray Effect® derived from the movement of a fish's tail fin.

Two flexible bands, which meet at the top like a triangle, form the basis of

the Fin Ray Structure®. The bands are connected by ribs, spaced at regular intervals, using flex hinges. This flexible but sturdy connection of the joints allows the gripper fingers to adapt to the contours of a workpiece.

Areas of application:



- Mechanical engineering
- Agriculture
- Man-machine cooperation

Adaptation options with the mounting kit DHAS-ME / mounting bracket DHAS-MA

The gripper fingers' interface is designed so that both parts can be easily slid together to form a positively-engaged and friction-based adapter while the fingers can flex.

The gripper finger can be mounted on an interface using the mounting kit DHAS-ME and a suitable adapter.

The gripper finger can be mounted on the parallel gripper HGPL-14 with the mounting kit DHAS-ME and the mounting bracket DHAS-MA.



- 1 Mounting kit DHAS-ME
- 2 Mounting bracket DHAS-MA
- 3 Adaptive gripper finger DHAS
- 4 Parallel gripper HGPL-14

Note

The following gripper types are particularly well-suited to using the adaptive gripper fingers:

- Long-stroke grippers
- Radial grippers
- Angle grippers

- The gripper finger is suitable for gripping rounded shapes
- The stroke per gripper jaw should be at least 10 mm

The gripper finger may become slightly deformed over the course of its service life. This does not have any influence on the gripper finger's functionality, however.

Adaptive gripper fingers DHAS


Features

FESTO

Sample applications


Transferring parts from tight packaging

- Different part diameters can be gripped in a form-fitting way with one gripper
- Gripping parts that are tightly packed with standard gripper jaws is difficult
- Thanks to the gripper fingers' pointed shape, they can be slid between the wall and the workpiece, even if the workpiece is off-centre




Step 1

Position the gripper fingers above the packaging




Step 2

Slide the gripper fingers into the packaging




Step 3

Wrap the fingers around the workpiece in a form-fitting way



Step 4

Lift the workpiece



Adaptive gripper fingers DHAS


Features

FESTO

Sample applications

Transferring sensitive parts such as filter cartridges

- Sensitive and fragile workpieces can be gripped smoothly
- Standard gripper jaws can damage workpieces during transfer
- Operating pressure can be adjusted using a proportional valve. This is particularly useful when the gripping force is distributed over several gripper fingers (less surface pressure)



Adaptive gripper fingers DHAS


Features

FESTO

Sample applications

Transferring unevenly shaped parts such as avocados

- Differently shaped parts can be gripped in an adaptive and smooth way without any need to change the gripper
- The option of having an internal block to reduce the stroke is particularly suitable if the workpiece forms vary significantly
- By varying the distance between the grippers, both the gripping force and the flex distance (the distance by which the fingers flex if pressed) can be adapted



Adaptive gripper fingers DHAS

Type codes


FESTO

		DHAS	–	GF	–	80	–	U	–	BU
Series										
DHAS	Gripper fingers									
Type										
GF	Fin jaw									
Size										
60	60									
80	80									
120	120									
Material										
U	Polyurethane									
Colour										
BU	Blue									

Adaptive gripper fingers DHAS

Technical data

FESTO



General technical data				
Size		60	80	120
Assembly position		Any		
Weights				
Gripper fingers	[g]	6.5	13	29
Angle bracket	[g]	23	38	59
Retainer	[g]	7	13	23
Screws	[g]	2.5	6	7
Clamping jaw materials		TPE-U (PU)		
Note on materials		Free of copper and PTFE		
		RoHS compliant		

Operating and environmental conditions				
Size		60	80	120
Ambient temperature	[°C]	10 ... 50		
Corrosion resistance class CRC ¹⁾		2		
Food suitability ²⁾		→ Advanced material information		


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


2) Additional information www.festo.com/sp → Certificates.

 Note


These gripper fingers are not designed for the following or similar examples of use:



- Machining
- Aggressive media



- Grinding dust




- Welding spatter

Adaptive gripper fingers DHAS

Technical data

FESTO

Max. retention force F_H as a function of gripping force F_G (of two gripper fingers) and workpiece diameter at 23°C




The retention force F_H is the maximum force that may be applied so that the gripper fingers can still hold the workpiece.

The values were determined under the following conditions:

- With parallel grippers HGPL-14
- Cylindrical workpiece


The values may differ under other ambient conditions (additional information on request).

Size 60




- Ø 6 mm
- - - Ø 20 mm
- · - · - Ø 40 mm
- · · · · Ø 50 mm

Size 80



- Ø 40 mm
- - - Ø 50 mm
- · - · - Ø 70 mm
- · · · · Ø 80 mm

Size 120




- Ø 70 mm
- - - Ø 80 mm
- · - · - Ø 100 mm
- · · · · Ø 120 mm

Adaptive gripper fingers DHAS

Technical data

FESTO

Max. lateral force F_Q as a function of gripping force F_G (of two gripper fingers) and workpiece diameter at 23°C




The lateral force F_Q is the maximum force that may be applied so that the workpiece does not begin to slip.

The values were determined under the following conditions:

- With parallel grippers HGPL-14
- Cylindrical workpiece
- In the middle of the gripper finger (MP2 → page 10)


The values may differ under other ambient conditions (additional information on request).

Size 60




- Ø 6 mm
- - - Ø 20 mm
- · - Ø 40 mm
- · · Ø 50 mm

Size 80



- Ø 40 mm
- - - Ø 50 mm
- · - Ø 70 mm
- · · Ø 80 mm

Size 120




- Ø 70 mm
- - - Ø 80 mm
- · - Ø 100 mm
- · · Ø 120 mm

Adaptive gripper fingers DHAS

Technical data

FESTO

Indentation depth t as a function of gripping force F_G (per gripper finger) at 23°C



- MP1 Measuring point 1
- MP2 Measuring point 2
- MP3 Measuring point 3
- MP4 Measuring point 4
- l Total length
- t Indentation depth


The values may differ under other ambient conditions (additional information on request).

Workpieces are best gripped in the middle of the gripper finger (MP2).


Size	l [mm]	MP1 [mm]	MP2 [mm]	MP3 [mm]	MP4 [mm]
60	50	15	25	35	50
80	80	30	40	50	80
120	115	47.5	57.5	67.5	115

Size	Indentation depth at MP2 [mm]
60	12
80	20
120	30


Size 60



Size 80



Size 120



- MP1
- - - MP2
- · - MP3
- MP4


Adaptive gripper fingers DHAS

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



Size	B1	B2	H1	L1
60	18	11.8	61.5	26
80	21.3	11.8	94.5	37.5
120	25	11.8	134.5	50

Ordering data

Size	Part No.	Type
60	3998967	DHAS-GF-60-U-BU
80	3998964	DHAS-GF-80-U-BU
120	3998959	DHAS-GF-120-U-BU

Adaptive gripper fingers DHAS

Accessories


FESTO

Mounting bracket DHAS-MA




Dimensions and ordering data


For size 60



For size 80



For size 120



- 1 Press-fit nut
for size 60: M3
for sizes 80 and 120: M4
- 2 Screw M3x8-10.9

For size	B1	B2	B3 ±0.2	B4 ±0.1	D1	D2 Ø	H1
60	27	4	3	6	M3	3.4	30.3
80	28.6	4	3	6	M4	3.3	35
120	30	3.6	3	6	M4	3.4	41.7

For size	H2	L1	L2 ±0.1	L3 ±0.1	L4	Part No.	Type
60	4	25.7	7	8	4.85	3920696	DHAS-MA-B6-60
80	4	34.5	12	8	5.25	3899099	DHAS-MA-B6-80
120	3.6	48	20	8	7.9	3889257	DHAS-MA-B6-120

Adaptive gripper fingers DHAS

Accessories


FESTO

Mounting kit DHAS-ME




Dimensions and ordering data

For sizes 60 and 80



For size 120



2 Screw

For size 60: ISO 4017-M3x22-A2-70

For size 80: ISO 4017-M4x25-A2-70

For size 120: ISO 4017-M4x30-A2-70

Dimensions

For size	B1	B2	B3 ±0.1	H1	H2	H3	H4
60	22.8	2.8	2	10.3	6.7	7	3.6
80	25.8	2.8	2	15.3	10.5	9	4.6
120	29.8	2.8	2	21.3	10.5	15	8.7

For size	H5 +0.1	L1	L2	L3 ±0.1	Part No.	Type
60	1.3	20.7	17.4	7	4464306	DHAS-ME-H9-60
80	1.3	31.4	26.4	12	4463570	DHAS-ME-H9-80
120	1.3	44.9	38	20	4461433	DHAS-ME-H9-120

Festo North America



**1 Festo Canada
Headquarters**
Festo Inc.
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters**
Festo Corporation
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com

Subject to change

Internet: www.festo.com/us